


MODU-C CS

The Modu-C CS can be individually configured according to customer requirements. All functions are available in both the containment and the non-containment version.



Modularity

Thanks to the patented trolley system, numerous products can be filled on just one machine – including a wide range of powders, pellets and liquids.



IPC station

The system weighs capsules during ongoing operation with an accuracy of +/- 0.1 mg. Quantity and frequency can be easily adjusted according to individual requirements.

HMI

Full HD Display with sophisticated design and user-friendly navigation structures.



100% gross control

Every filled capsule is weighed during ongoing operation. The weighing accuracy is +/- 2 mg.

Deduster

An integrated deduster removes even very small residual powder quantities from the capsule shell. An external deduster is not required and the footprint is considerably reduced.



Helmar Lünig

Containment

The system provides protection concepts for every field of application, even for powder OEL < 1µg/OEB 5. This guarantees the highest operator protection.



Wet-in-Place

Special technology enables safe cleaning of the interior. This involves the use of spray mist from up to 10 l of water per passage.